


# VLOG RING LIGHT WITH PHONE HOLDER

Instruction Manual

108098338

## INCLUDED

- Vlog light with phone holder
- Instruction manual



## SPECIFICATIONS

Light mode:	Warm light, cool light, daylight
Colour temperature:	3000-6500 K
Ring light:	15.56cm (6 1/8in)
Power Source:	DC 5V/1A
Cable length:	170.18cm (67in)

CAN ICES-005(B)/NMB-005(B)

## FEATURES

- 10 brightness levels
- 3 colour modes: warm, daylight and cool
- Foldable and lightweight
- Built-in makeup mirror
- Supports portrait and landscape phone placement

## GETTING STARTED

### OPERATING INSTRUCTIONS

1. Plug the USB into a 5V/1A power source (wall charger, laptop, etc.).
2. Press the ON/OFF button to turn the light ON.
3. Press the + button to increase the brightness of the light one level at a time. Press and hold to gradually increase the brightness.
4. Press the - button to decrease the brightness of the light one level at a time. Press and hold to gradually decrease the brightness.
5. Press the colour mode button to cycle through the 3 colour modes: warm, daylight and cool.



## THE SOURCE - WARRANTY

The Source warrants that this product will be free from defects in materials and workmanship for a period of (6) six months from the date of purchase. Within this period, simply take the product and your proof of purchase to any The Source store or participating dealer and the product will be replaced (where available) without charge. Any product which has been subject to misuse or accidental damage is excluded from this warranty.

This warranty is only applicable to a product purchased through The Source company-owned stores or participating dealers in Canada where the warranty is included with the product. While this warranty does not confer any legal rights other than those set out above, you may have additional statutory rights which will vary under the laws of the various countries, states, provinces and other governmental entities in which The Source operates. This warranty is subject to all statutory rights you may have in Canada.

Imported by:  
The Source, Barrie, Ontario, Canada, L4M 4W5  
Manufactured in China  
www.thesource.ca  
© 2022 The Source. All rights reserved.

